

## INSTALLATION NOTE

### F100A Mimic Escutcheon Plate

#### Feature Overview:

The F100A Mimic Escutcheon Plate allows the F100A LCD Full Function Mimic to be flush-mounted in the wall cavity.

#### Dimensions:

Outer 413mm x 240mm x 1mm (W x H x D)

Inner 350mm x 178mm (W x H)

#### Mounting:

1. Remove the four countersunk machine screws on the top and bottom of F100A LCD Mimic.
2. Locate the existing dwang inside the chosen wall location, or be prepared to add a horizontal support member inside the wall.
3. Cut the correct-sized hole in the wall board. Add or locate a suitable rear mounting surface for the F100A Mimic.
4. Secure the F100A Mimic—there are two mounting holes suitable for screw head mounting.
5. Replace the four machine screws, through the Escutcheon Plate, into the original holes of the F100A Mimic.

